

# MATTRESS BAG SEALING MACHINE SM210A

HEAT SEALS MATTRESS PLASTIC BAGS



## introduction

A practical,  
easy and simple method  
to heat seal mattress  
plastic bags.

## mattress bag sealing machine

Up to 210 cm wide bags can be sealed.

Fully adjustable heating and cooling time.

The operation can be initiated by a pedal switch.

The machine is supplied without the loading table.

Height of sealing: 82 cm from floor level.

Recommended table height: 72 cm.

Safety sensors stop the closing of the jaws in case of blockage.

The preheating of the element and the pneumatically controlled jaw movement guarantee constant sealing results.

## model SM210A



## operation

The mattress having been inserted into the plastic bag, is then placed on the loading table (not provided). The open part of the bag is passed through the machine jaws and is held in position. Using the pedal switch the machine seals the bag. The plastic waste can be pulled to be cut before the machine resets itself. Illuminating indicators guide the operator through the above procedure.




Electrical supply: 220V, 2kW

Compressed air: 6 bar maximum

Shipping Weight: 210 kg

Dimensions: 250 x 80 x 100 cm height

### Working space required



Offices and Factory

39, Kalamon Street  
2032 Strovolos Industrial Zone  
Nicosia - CYPRUS

Tel. +357 22 484444  
Fax +357 22 481360

Postal Address

P.O.Box 22361  
1520 Nicosia  
CYPRUS

E-Mail : [info@amelco.com](mailto:info@amelco.com)  
<http://www.amelco.com>